

LMC6062P Green for Glass / Ceramic Laser Settings



USA Tel: (336) 288-1613 Toll Free (866) 288-1613
sales@jorlink.com or support@jorlink.com

Laser Settings for LMC6062P Materials

The following table details recommended laser settings for LMC6062P materials on glass and ceramic. These settings are designed to help guide the user to the optimum parameters as quickly as possible. Please note that there will be variations in substrate finish and between different brands of laser. It may still be necessary to perform further refinement of settings to achieve the desired mark.

LMC6062P Suggested Laser Settings Used for CO ₂ X-Y Laser						
Substrate Material	Settings 45W laser		Settings 30W laser		Lens	DPI/PPI
	Power (W)	Speed (in/sec)	Power (W)	Speed (in/sec)		
Glass	4	28	4	28	2"	600/600
Ceramic	14	42	14	42	2"	600/600

Suggested Laser Settings Used for Beam Steered ND:YAG or Fiber Laser with a 100mm lens				
Material	Power (W)	Speed (cm/sec)	Hatch Spacing "	CW Mode or Q-Switch Freq
Glass	7	15	0.002	CW / ≥50KHz
Ceramic	6	5	0.002	CW / ≥50KHz



USA Tel: (336) 288-1613 Toll Free (866) 288-1613
sales@jorlink.com or support@jorlink.com